


IFC231

Inductive sensor

IFG3004-BNKG/M/5V/0,46M/PH/



Article no longer available - archive entry



Product characteristics

Electrical design		NPN
Output function		normally closed
Sensing range	[mm]	4
Housing		cylindrical
Dimensions	[mm]	Ø 12

Application

Application	Use in machine tools, coolants and lubricants
-------------	---

Electrical data

Operating voltage tolerance	[%]	10
Operating voltage	[V]	5 DC
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		no

IFC231



Inductive sensor

IFG3004-BNKG/M/5V/0,46M/PH/

Outputs		
Electrical design		NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	0.4
Max. leakage current	[mA]	0.1
Permanent current rating of switching output DC	[mA]	10
Switching frequency DC	[Hz]	700
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	4
Operating distance	[mm]	0...3.25
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...20
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 68; ("Coolant")
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Mechanical data		
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 12
Materials		sensing face: LCP; housing: stainless steel; Angle brackets: stainless steel; LED window: PEI
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

IFC231




Inductive sensor

IFG3004-BNKG/M/5V/0,46M/PH/

Electrical connection

Cable: 0.46 m, PUR / PVC; 3 x 0.34 mm²

Connection



Core colours :

BK = black
BN = brown
BU = blue

Article no longer available - archive entry