
# TM4331

# Temperature sensor with process connection

/US/

TM-100KFBN12-







Product characteristics				
Measuring range		-40150 °C	-40302 °F	
Process connection			threaded connection 1/2" NPT	
Installation length EL	[mm]		100	
Application				
Special feature			Gold-plated contacts	
Measuring element		1 x I	Pt 100; (to DIN EN 60751, class A)	
Media			liquids and gases	
Pressure rating	[bar]		160	
Minimum installation depth	[mm]		15	
Electrical data				
Protection class			III	
Measuring/setting range				
Probe length L	[mm]		92	
Measuring range		-40150 °C	-40302 °F	
Accuracy / deviations				
Accuracy	[K]		± (0,15 K + 0,002 x t )	
Response times				
Dynamic response T05 / T09	[s]		1 / 3; (to DIN EN 60751)	
Operating conditions				
Ambient temperature	[°C]		-2580	
Storage temperature	[°C]		-40100	
Protection			IP 68; IP 69K	
Tests / approvals				
Shock resistance		DIN EN 60068-2-2-27	50 g (11 ms)	
Vibration resistance		DIN EN 60068-2-6	10 g (102000 Hz)	
MTTF	[years]		22831	
Mechanical data				
Weight	[g]		144.5	

# TM4331

## Temperature sensor with process connection

TM-100KFBN12-

/US/



Materials		stainless steel (316L/1.4404)
Materials (wetted parts)		stainless steel (316L/1.4404)
Process connection		threaded connection 1/2" NPT
Probe diameter	[mm]	6
Installation length EL	[mm]	100

Remarks		
Remarks	operating voltage "supply class 2" according to cULus	
	The values for accuracy apply to flowing water.	
Pack quantity	1 pcs.	

## **Electrical connection**

Connector: 1 x M12; coding: A; Contacts: gold-plated



## Connection

