


AC1346



AS-Interface PROFIBUS DP gateway with PLC

ControllerE 2Mstr DP RS232

Article no longer available - archive entry



1 Display



Application	
Application	decentralised controller; PROFIBUS DP gateway
Electrical data	
Operating voltage [V]	24 DC
Insulation rating [V]	500
Current consumption [mA]	< 500
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	2
Electrical separation	yes
Interfaces	
Communication interface	RS232; PROFIBUS

AC1346



AS-Interface PROFIBUS DP gateway with PLC

ControllerE 2Mstr DP RS232

PROFIBUS		
Transmission standard	EN 50170	
Transmission rate	12 MBaud	
Protocol	Profibus DP	
Usage type	data transmission	
Addition	diagnostic function	
RS232		
Number of R232 interfaces	1	
Transmission rate	9600...115200 Baud	
Connector type	RJ11	
Usage type	programming	
Addition	electrically isolated	
Operating conditions		
Ambient temperature [°C]	0...60	
Storage temperature [°C]	-20...70	
Max. relative air humidity [%]	95	
Protection	IP 20	
AS-i classification		
AS-i version	2.1	
AS-i profile	M3	
AS-i certificate pending	yes	
Mechanical data		
Housing	housing for DIN rail mounting	
Dimensions [mm]	86 x 131 x 107	
Materials	aluminium; steel sheet galvanised	
Displays / operating elements		
Display	function	3 x LED, red
		3 x LED, green
		3 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity	1 pcs.	

AC1346



AS-Interface PROFIBUS DP gateway with PLC

ControllerE 2Mstr DP RS232

Electrical connection

Connection



Article no longer available - archive entry