

AC2004




AS-Interface module

ASI-MODUL-OBERTEIL M12 4AR

Article no longer available - archive entry

Alternative article: AC5213 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



1 panel for labelling



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 35
Max. current load total	[A]	2
Integrated watchdog		no

Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 4
------------------------------	----------------------------

Outputs

Electrical design		AS-i
Voltage range DC	[V]	24; (to PELV; via M12 connector)
Max. current load per output	[mA]	1000
Number of relay outputs		4
Short-circuit proof		no
Electrically separated		yes

Operating conditions

Ambient temperature	[°C]	-25...85
Protection		IP 67

Tests / approvals


EMC	EN 50295
-----	----------

AC2004



AS-Interface module

ASI-MODUL-OBERTEIL M12 4AR

AS-i classification					
AS-i profile	S-8.0				
AS-i I/O configuration [hex]	8				
AS-i ID code [hex]	0				
Assignment of the data bits	data bit	D0	D1	D2	D3
	socket	O-1	O-2	O-3	O-4
	pin	4	4	4	4
Mechanical data					
Type of mounting	AS-i interface to FC lower parts				
Materials	PBT				
Displays / operating elements					
Display	operation	LED, green			
	function	LED, yellow			
Remarks					
Pack quantity	1 pcs.				
Electrical connection					
contact pins to module lower part, FK / PG:					
1	external voltage +				
3	external voltage -				
Connector: M12					
Connector: M12					
					

Article no longer available - archive entry

Alternative article: AC5213 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!