


IGA3005-APKG



PNP

verbreekcontact

5

cilindrisch schroefdraad

M18 x 1 / L = 80

[M]

10...36 DC

[mA]

15; (24 V)

11

ja

PNP

verbreekcontact

[M]

2,5

[mA]

250

[Hz]

500

ja

pulserend

ja

[mm]

5

[mm]

 $5 \pm 10 \%$

[mm]

0...4,05

staal: 1 / roestvast staal: 0,7 / messing: 0,4 / aluminium: 0,3 / koper: 0,2

[% van Sr]

1...15

[% van Sr]


-10...10



Inductieve sensor

IGA3005-APKG

Omgevingsvariabelen		
Omgevingstemperatuur	[°C]	-25...80
Beschermklasse		IP 67
Toelatingen / testen		
EMC	EN 60947-5-2	
	EN 55011	klasse B
MTTF	[jaren]	1874
Mechanische eigenschappen		
Gewicht	[g]	157,3
Behuizing		cilindrisch schroefdraad
Inbouwwijze		bondig inbouwbaar
Afmetingen	[mm]	M18 x 1 / L = 80
Schroefdraadtype		M18 x 1
Materialen		messing wit-brons gecoat; PC
Aanwijzen / bedienelementen		
Weergave	schakelstatus	1 x LED, geel
Toebehoren		
Leveringsomvang		bevestigingsmoeren: 2
Opmerkingen		
Verpakkingseenheid		1 stuk
Elektrische aansluiting		
Kabel: 2 m, PVC; 3 x 0,5 mm²		
Aansluiting		



BN = Aderkleuren :
 BU = bruin
 BK = blauw
 zwart