







Incrementele pulsgever met holle as

RO-2500-I05/N11

Toelatingen / testen		
Schokbestendigheid		100 g (6 ms)
Trillingsbestendigheid		10 g (55...2000 Hz)
Mechanische eigenschappen		
Afmetingen	[mm]	Ø 58 / L = 55
Materialen		aluminium
Max. toerental mechanisch	[U/min]	12000
Max. aandraaimoment	[Nm]	2,5
Referentietemperatuur aandraaimoment	[°C]	20
As uitvoering		Doorgaand asgat
Asdiameter	[mm]	10
As passing		H7
Materiaal as		RVS
Inbouwdiepte van de as	[mm]	10
Max. axiale asverplaatsing	[mm]	1; (max. radiale as uitlijning : ± 0,05 mm)
Elektrische aansluiting		
Kabel: 1 m, PUR; radiaal		
bruin	A	
groen	A geïnverteerd	
grijs	B	
rose	B geïnverteerd	
rood	0-index	
zwart	0-index geïnverteerd	
blauw	L+ sensor	
wit	0V sensor	
bruin / groen	L+ (Up)	
wit / groen	0V (Un)	
violet	storing geïnverteerd	
afscherming	behuizing	
Diagrammen en curves		
Impulsdiagram	 draairichting met de klok mee op de as gezien	