


DX2041



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC



panel
cutout 91 x 43 mm



Product characteristics

Dimensions	[mm]	48 x 112 x 116
------------	------	----------------

Application

Application	displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors
-------------	--

Electrical data

Frequency AC	[Hz]	50...60
Operating voltage	[V]	115...230 AC / 18...30 DC
Current consumption	[mA]	100

Inputs / outputs

Number of inputs and outputs	Number of analogue inputs: 2
------------------------------	------------------------------

Inputs

Number of analogue inputs	2; (Spannungs- oder Stromeingang)	
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	-10...10
Resolution of analogue input		16 bit
Precision analogue input	[%]	0,1

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...70
Protection		IP 65
Protection rating terminals		IP 20

Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-3	
	EN 61000-6-4	

Mechanical data

Weight	[g]	351
--------	-----	-----



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC	
Type of mounting	panel cutout: 91 x 43 mm
Dimensions [mm]	48 x 112 x 116
Materials	Noryl UL94-V-0


Displays / operating elements

Display	colour display	full graphic LCD display, touch screen
---------	----------------	--

Electrical connection

screw terminals:

Connection



NC not used