


E12363



Connection cable

VDOGH050MSA0015C05STGH050MSS



Application

Special feature	Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
Application	CAN bus

Electrical data

Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load total	[A]	4

Operating conditions

Ambient temperature	[°C]	-25...85
Storage temperature	[°C]	-40...80
Protection		IP 68

Mechanical data

Weight	[g]	1085
Dimensions	[mm]	14.5 x 14.5 x 48.5
Materials		PUR
Moulded-body material		PUR
Material nut		diecast zinc, nickel-plated
Drag chain suitability		yes
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	bending radius for fixed installation	min. 5 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²
	bending cycles	> 1 Mio.

Remarks


Pack quantity	1 pcs.
---------------	--------

Connection cable

VDOGH050MSA0015C05STGH050MSS

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: diecast zinc, nickel-plated; Contacts: gold-plated; Tightening torque: 0.5 Nm




Electrical connection

Cable: 15 m, PUR, Halogen-free, lilac, Ø 7.2 mm, shielded; twisted; 2 (RD) / 3 (BK): 2 x 0.25 mm² (19 x Ø 0.13 mm) / twisted + 4 (WH) / 5 (BU): 2 x 0.34 mm² (19 x Ø 0.16 mm) / twisted

Cable: 15 m, PUR, Halogen-free, lilac, Ø 7.2 mm, shielded; 1: 1 x 0.34 mm² (19 x Ø 0.16 mm)

Connection



Core colours :
 BK = black
 BU = blue
 RD = red
 WH = white
 screen = screen

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: diecast zinc, nickel-plated; Contacts: gold-plated; Tightening torque: 0.5 Nm

