


KQ6007



Capacitive sensor

KQ-3120NFPKG/2T/10M



- 1 Sensing face
- 2 programming buttons
- 3 LED



Product characteristics

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	12
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	20 x 14 x 48

Application

Installation	detection through non-metallic container wall or on bypass pipes
Media	dry bulk material; liquids

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 17
Protection class	III
Reverse polarity protection	yes
Measuring principle	capacitive

Outputs

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10
Short-circuit protection	yes



Capacitive sensor

KQ-3120NFPKG/2T/10M

Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Sensing range	[mm]	12
Real sensing range Sr	[mm]	12 ± 10 %
Accuracy / deviations		
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-20...20
Interfaces		
Communication interface	IO-Link	
Transmission type	COM1 (4,8 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor	
SIO mode	yes	
Min. process cycle time	[ms]	100.8
Supported DeviceIDs	Type of operation	DeviceID
	default	371
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 65; IP 67; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Shock resistance	EN 60068-2-27	30 g 6 shocks / 11 ms half-sine (x, y, z)
Vibration resistance	EN 60068-2-6	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
MTTF	[years]	725
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
Mechanical data		
Weight	[g]	144.3
Housing	rectangular	
Mounting	non-flush mountable	
Dimensions	[mm]	20 x 14 x 48
Materials	housing: PBT glass fibre reinforced; pushbuttons: TPE-U; cover: PC glass fibre reinforced	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Teach function	yes	

KQ6007



Capacitive sensor

KQ-3120NFPKG/2T/10M

Electronic lock	yes
-----------------	-----


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 10 m, PVC; 3 x 0.14 mm²

Connection



BK:	OUT / IO-Link
	Core colours :
BK =	black
BN =	brown
BU =	blue