


# LI5131



## Sensor for point level detection

LI0132--K-00KQPKG/US



- 1 LEDs
- 2 inductive programming button



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Factory setting	hydrous media
Probe length L [mm]	132

### Application

Special feature	Gold-plated contacts
Media	Liquids
Dielectric constant of the medium	> 1,8
Recommended media	water; hydrous media; oils; oil-based media
Cannot be used for	See operating instructions, chapter "Intended use".
Medium temperature [°C]	-25...85
Pressure rating [bar]	0.5
Vacuum resistance [mbar]	-500

### Electrical data

Operating voltage [V]	9.6...35 DC; (IO-Link: 18...30 DC)
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 1
Measuring principle	capacitive

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

# LI5131



## Sensor for point level detection

LI0132--K-00KQPKG/US

Outputs		
Total number of outputs		2
Output signal		switching signal; IO-Link
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Factory setting		hydrous media
Probe length L	[mm]	132
Active range A	[mm]	28
Temperature measurement		
Measuring range	[°C]	-25...85
Accuracy / deviations		
Temperature measurement		
Accuracy	[K]	1,5
Resolution	[K]	0.1
Dynamic response T09	[s]	240
Response times		
Response time	[s]	< 0.3
Interfaces		
Communication interface		IO-Link
Unterstützte Masterportklasse		A
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor ED2: Identification and Diagnosis (0x4000), Measurement Data Channel (0x800A)
SIO mode		yes
Process data analogue		5
Process data binary		2
Min. process cycle time	[ms]	4.5
Supported DeviceIDs	<b>Type of operation</b>	<b>DeviceID</b>
	default	1053
Operating conditions		
Ambient temperature	[°C]	-25...85
Storage temperature	[°C]	-25...85

# LI5131



## Sensor for point level detection

LI0132--K-00KQPKG/US

Protection	IP 68; IP 69K; (7 days / 3 m water depth / 0.3 bar: IP 68)
------------	--

### Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	in a closed metal tank
	DIN EN 61000-6-4	in plastic or open metal tanks
Shock resistance	DIN EN 60068-2-27	12 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]		433
UL approval	UL Approval no.	H013
	File number UL	E174191

### Mechanical data

Weight [g]	203.55
Materials	PP reinforced fibre
Materials (wetted parts)	PP
Probe diameter [mm]	16

### Displays / operating elements

Display	operation	LED, green
	switching status	LED, yellow
Operating elements	inductive programming button	

### Remarks


Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1: switching output  
OUT2: switching output