


Through-beam sensor receiver

OUE-HNKG

Article no longer available - archive entry



receiver in upper lens

Product characteristics

Housing	rectangular
---------	-------------

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	20; ((24 V))
Protection class		II
Reverse polarity protection		yes

Outputs

Electrical design		NPN
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	140
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Transmitter / receiver		receiver
Range	[m]	< 6
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B



Through-beam sensor receiver

OUE-HNKG

Mechanical data		
Weight	[g]	0.155
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass

Displays / operating elements		
Display	switching status	1 x LED, yellow



Accessories		
Items supplied	Angle bracket: 1, E20211	

Remarks		
Pack quantity	1 pcs.	

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm²

Connection



BN = Core colours :
BU = brown
BK = blue
BK = black