


# PM1504



## Electronic pressure sensor

PM-010-REA12-A-ZVG/US



- 1 Gasket FKM (for sealing on the back - not pressure resistant) / removable
- 2 pre-mounted PEEK sealing ring (removable) / metallic sealing area
- 3 groove for sealing ring DIN 3869-21



### Product characteristics

|                    |  |                 |              |
|--------------------|--|-----------------|--------------|
| Measuring range    | -1...10 bar  | -14.5...145 psi | -0.1...1 MPa |
| Process connection | threaded connection G 1/2 external thread sealing cone |                 |              |

### Application

|                            |   |          |         |
|----------------------------|---|----------|---------|
| Special feature            | Gold-plated contacts  |          |         |
| Measuring element          | ceramic-capacitive pressure measuring cell                            |          |         |
| Temperature monitoring     | yes   |          |         |
| Application                | flush mountable for the food and beverage industry                    |          |         |
| Media                      | viscous media and liquids with suspended particles; liquids and gases |          |         |
| Conditionally suitable for | use in gases at pressures > 25 bar only on request                    |          |         |
| Medium temperature [°C]    | -25...125; (< 1 h: 150)   |          |         |
| Min. bursting pressure     | 175 bar   | 2538 psi | 17 MPa  |
| Pressure rating            | 75 bar  | 1100 psi | 7.5 MPa |
| Vacuum resistance [mbar]   | -1000   |          |         |
| Type of pressure           | relative pressure; vacuum   |          |         |
| No dead space              | yes   |          |         |

# PM1504



## Electronic pressure sensor

PM-010-REA12-A-ZVG/US

| Electrical data                    |                        |  |                                   |
|------------------------------------|------------------------|--|-----------------------------------|
| Operating voltage                  | [V]                    | 18...30 DC   |                                   |
| Min. insulation resistance         | [MΩ]                   | 100; (500 V DC)  |                                   |
| Protection class                   |                        | III  |                                   |
| Reverse polarity protection        |                        | yes  |                                   |
| Integrated watchdog                |                        | yes  |                                   |
| 2-wire                             |                        |  |                                   |
| Current consumption                | [mA]                   | 3.5...21.5   |                                   |
| Power-on delay time                | [s]                    | < 1  |                                   |
| 3-wire                             |                        |  |                                   |
| Current consumption                | [mA]                   | < 45   |                                   |
| Power-on delay time                | [s]                    | < 0.5  |                                   |
| Outputs                            |                        |  |                                   |
| Total number of outputs            |                        | 2  |                                   |
| Output signal                      |                        | analogue signal; IO-Link   |                                   |
| Analogue current output            | [mA]                   | 4...20; (scalable; 1:5)  |                                   |
| Max. load                          | [Ω]                    | 700; (U <sub>b</sub> = 24 V; (U <sub>b</sub> - 9 V) / 21.5 mA)                                     |                                   |
| Short-circuit proof                |                        | yes  |                                   |
| Overload protection                |                        | yes  |                                   |
| Measuring/setting range            |                        |  |                                   |
| Measuring range                    |                        | -1...10 bar  | -14.5...145 psi<br>-0.1...1 MPa   |
| Analogue start point               |                        | -1...8 bar   | -14.5...116 psi<br>-0.1...0.8 MPa |
| Analogue end point                 |                        | 1...10 bar   | 14.5...145 psi<br>0.1...1 MPa     |
| In steps of                        |                        | 0.005 bar  | 0.1 psi<br>0.0005 MPa             |
| Factory setting                    |                        | ASP = 0.0 bar  | AEP = 10.0 bar                    |
| Temperature monitoring             |                        |  |                                   |
| Measuring range                    |                        | -25...150 °C   | -13...302 °F                      |
| Accuracy / deviations              |                        |  |                                   |
| Repeatability                      | [% of the span]        | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)                                     |                                   |
| Characteristics deviation          | [% of the span]        | < ± 0,5; (linearity incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1) |                                   |
| Linearity deviation                | [% of the span]        | < ± 0,15; (Turn down 1:1)  |                                   |
| Hysteresis deviation               | [% of the span]        | < ± 0,15; (Turn down 1:1)  |                                   |
| Long-term stability                | [% of the span]        | < ± 0,1; (Turn down 1:1; per year)   |                                   |
| Temperature coefficient zero point | [% of the span / 10 K] | < ± 0,1 (-25...85 °C); < ± 0,3 (85...150 °C)   |                                   |
| Temperature coefficient span       | [% of the span / 10 K] | < ± 0,1 (-25...85 °C); < ± 0,3 (85...150 °C)   |                                   |
| Temperature monitoring             |                        |  |                                   |
| Accuracy                           | [K]                    | ± 2.5 K + (0.045 x (ambient temperature - medium temperature))                                     |                                   |

# PM1504



## Electronic pressure sensor

PM-010-REA12-A-ZVG/US

| Response times                      |   |  |
|-------------------------------------|---|--|
| Damping for the analogue output dAA | [s]   | 0...4  |
| 2-wire                              |   |  |
| Step response time analogue output  | [ms]  | 30   |
| 3-wire                              |   |  |
| Step response time analogue output  | [ms]  | 7  |
| Temperature monitoring              |   |  |
| Dynamic response T05 / T09          | [s]   | < 10 / < 25; (DIN EN 60751 water; > 0,9 m/s) |
| Interfaces                          |   |  |
| Communication interface             | IO-Link   |  |
| Transmission type                   | COM2 (38,4 kBaud)   |  |
| IO-Link revision                    | 1.1   |  |
| SDCI standard                       | IEC 61131-9   |  |
| Profiles                            | Smart Sensor ED2: Identification and Diagnosis (0x4000), Measurement Data Channel (0x800A)                                |  |
| SIO mode                            | no  |  |
| Required master port type           | A; (when pin 2 not connected: B)  |  |
| Min. process cycle time             | [ms]  | 4.5  |
| IO-Link resolution pressure         | [bar]   | 0.002  |
| IO-Link resolution temperature      | [K]   | 0.2  |
| IO-Link process data (cyclical)     | function  | bit length                                   |
|                                     | pressure  | 16   |
|                                     | temperature   | 16   |
|                                     | device status   | 4  |
| IO-Link functions (acyclical)       | application specific tag; internal temperature  |  |
| Supported DeviceIDs                 | Type of operation   | DeviceID                                     |
|                                     | Default   | 1021   |
| Operating conditions                |   |  |
| Ambient temperature                 | [°C]  | -25...80                                     |
| Storage temperature                 | [°C]  | -40...100                                    |
| Protection                          | IP 67; IP 68; IP 69K  |  |
| Tests / approvals                   |   |  |
| EMC                                 | DIN EN 61326-1  |  |
| Shock resistance                    | DIN EN 60068-2-27   | 50 g (11 ms)                                 |
| Vibration resistance                | DIN EN 60068-2-6  | 20 g (10...2000 Hz)                          |
| MTTF                                | [years]   | 322  |
| Note on approval                    | factory certificate available as download at <a href="http://www.factory-certificate.ifm">www.factory-certificate.ifm</a> |  |
| UL approval                         | UL Approval no.   | J024   |
|                                     | File number UL  | E174189                                      |

# PM1504



## Electronic pressure sensor

PM-010-REA12-A-ZVG/US


| Mechanical data          |   |
|--------------------------|---|
| Weight [g]               | 307.4   |
| Materials                | stainless steel (1.4404 / 316L); PTFE; FKM  |
| Materials (wetted parts) | ceramics (99.9 % Al <sub>2</sub> O <sub>3</sub> ); stainless steel (1.4435 / 316L);<br>surface characteristics: Ra < 0,4 / Rz 4; PEEK; PTFE |
| Min. pressure cycles     | 100 million   |
| Tightening torque [Nm]   | 20  |
| Process connection       | threaded connection G 1/2 external thread sealing cone  |
| Remarks                  |   |
| Pack quantity            | 1 pcs.  |

## Electrical connection

Connector: 1 x M12; Contacts: gold-plated



## Connection



- 1 connection for 2-wire operation ( analogue )
- 2 connection for 3-wire operation ( analogue / IO-Link )  
OUT1: IO-Link  
OUT2: analogue output