


PQS819



Pressure sensor for pneumatics

PQ-0-1BKHR18-MFPKG/AS/



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-1...0 bar	-100...0 kPa
Process connection	threaded connection G 1/8 internal thread (2x)	
Application		
Special feature	Gold-plated contacts	
Application	for industrial applications	
Media	compressed air; nitrogen (N2)	
Conditionally suitable for	other media on request	
Medium temperature [°C]	0...60	
Min. bursting pressure	30 bar	3 MPa
Pressure rating	10 bar	1 MPa
Vacuum resistance [mbar]	-1000	
Type of pressure	relative pressure; vacuum	



Pressure sensor for pneumatics

PQ-0-1BKHR18-MFPKG/AS/

Electrical data			
Operating voltage	[V]	18...30 DC	
Current consumption	[mA]	< 30	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Overvoltage protection		yes; (< 40 V)	
Power-on delay time	[s]	0.3	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	
Outputs			
Total number of outputs		2	
Output signal		switching signal; IO-Link; (configurable)	
Electrical design		PNP/NPN; (configurable)	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	100	
Switching frequency DC	[Hz]	< 170	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range	-1...0 bar	-100...0 kPa	
Set point SP	-1...0 bar	-100...0 kPa	
In steps of	0.001 bar	0.1 kPa	0.0001 MPa
Accuracy / deviations			
Switch point accuracy		< ± 1	
	[% of the span]		
Repeatability		< ± 0,1; (with temperature fluctuations < 10 K:)	
	[% of the span]		
Characteristics deviation		< ± 1; (including linearity, hysteresis and repeatability)	
	[% of the span]		
Linearity deviation		< ± 1 % (limit value setting to DIN EN IEC 62828-1)	
	[% of the span]		
Hysteresis deviation		< ± 0,25	
	[% of the span]		
Long-term stability		< ± 0,1; (per year)	
	[% of the span]		
Temperature coefficient zero point		0,2	
	[% of the span / 10 K]		
Temperature coefficient span		0,2	



Pressure sensor for pneumatics

PQ-0-1BKHR18-MFPKG/AS/

[% of the span / 10 K]

Response times		
Response time	[ms]	6
Damping process value dAP	[s]	0...4
Damping for the analogue output dAA	[s]	0...99.99
Software / programming		
Parameter setting options	display can be rotated and switched off; Teach function; simulation function; diagnostic function	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9: 2019-06	
Profiles	Identification and Diagnosis (0x4000), Measurement Data Channel (0x800A), SSP 4.1.1 (0x0010), Quantity detection nach Smart Sensor Profil (0x8014)	
SIO mode	yes	
Required master port type	A	
Process data analogue	1	
Process data binary	2	
Min. process cycle time	[ms]	0.6
IO-Link resolution pressure	[bar]	0.0001
IO-Link process data (cyclical)	function	bit length
	pressure	16
	device status	4
	SSC1.1	1
	SSC1.2	1
IO-Link functions (acyclical)	application specific tag; internal temperature; Medium temperature	
Supported DeviceIDs	Type of operation	DeviceID
	default	1745
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-25...85
Protection	IP 65	
Tests / approvals		
EMC	DIN EN 61326-1	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	508
Pressure Equipment Directive	Sound engineering practice; can be used for stable gases fluid group 2	
Mechanical data		
Weight	[g]	0.001
Materials	PBT; PC; TPE; NBR; FKM; brass; silicon (coated)	
Materials (wetted parts)	PBT; FKM; brass; silicon (coated)	
Min. pressure cycles	50 million	

PQS819



Pressure sensor for pneumatics

PQ-0-1BKHR18-MFPKG/AS/


Process connection	threaded connection G 1/8 internal thread (2x)	
Displays / operating elements		
Display	Display 1"	128 x 96 pixels
	switching status	2 x LED, yellow
Display unit	bar; MPa; mmHg; kgf/cm²	
Remarks		
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M8; coding: A; Contacts: gold-plated



Connection



OUT1 switching output / IO-Link
OUT2 switching output
 colours to DIN EN 60947-5-2
 Core colours
BK= black
BN= brown
BU= blue
WH= white

Diagrams and graphs

Bohrbild

