
IY5052

Inductive sensor

IYB31,2-BPKG/V2A



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	1.2
Housing		threaded type
Dimensions	[mm]	M5 x 0.5 / L = 23
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	1.2
Operating distance	[mm]	0...0.97
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 65

IY5052


Inductive sensor

IYB31,2-BPKG/V2A

Tests / approvals			
EMC		EN 60947-5-2	
Mechanical data			
Weight	[g]	35	
Housing		threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M5 x 0.5 / L = 23	
Thread designation		M5 x 0.5	
Materials		stainless steel (1.4305 / 303); POM	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue