


NI5010



Inductive sensor

IIA2015-N/20M

Article no longer available - archive entry



Product characteristics

Electrical design		NAMUR
Output function		normally closed
Sensing range	[mm]	15
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 41

Electrical data

Connection to switching amplifiers		yes
Switching amplifiers		connection to switching amplifiers NV0100, NV0200 or other approved switching amplifiers with the max. values: U = 16 V / I = 50 mA / P = 180 mW (T5) / P = 123 mW (T6)
Nominal voltage DC	[V]	8.2; (1k Ω)
Supply voltage DC	[V]	5...25
Current consumption	[mA]	< 1; (disabled; conductive: > 2,1)

Outputs

Electrical design		NAMUR
Output function		normally closed
Max. cable resistance	[Ω]	50
Switching frequency DC	[Hz]	200

Detection zone

Sensing range	[mm]	15
---------------	------	----

Operating conditions

Ambient temperature	[$^{\circ}$ C]	-20...70
Protection		IP 67

Tests / approvals

Approval		PTB-Zulassungs-Nr. Ex-00.E.2013; Gerätekennzeichnung: EEx ia IIC T5/T6
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)
MTTF	[years]	4697


NI5010



Inductive sensor

IIA2015-N/20M

Safety classification	
Max. internal capacitance [nF]	240
Max. internal inductance [µH]	140
Mechanical data	
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M30 x 1.5 / L = 41
Thread designation	M30 x 1.5
Materials	brass nickel-plated; PBT
Accessories	
Items supplied	lock nuts: 2
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 20 m, PVC; 2 x 0.5 mm ²	
Connection	



Core colours :

BN = brown
BU = blue