




## Retro-reflective sensor

OUR-DNKG/US-100-DNS

Article no longer available - archive entry



receiver in upper lens  
transmitter in lower lens

### Product characteristics

Type of light	infrared light
Housing	rectangular
Dimensions [mm]	28 x 16 x 51

### Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

### Electrical data

Operating voltage [V]	10...50 DC
Current consumption [mA]	35; ((24 V))
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

### Outputs

Electrical design	NPN
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	160
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

### Detection zone

Range [m]	0.15...3; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Max. light spot diameter [mm]	262
Light spot dimensions refer to	at maximum range

# OU5078



## Retro-reflective sensor

OUR-DNKG/US-100-DNS


Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		Angle bracket: 1 x, E20211
Remarks		
Pack quantity		1 pcs.

### Electrical connection

Connector: 1 x M12



### Connection






## Retro-reflective sensor

OUR-DNKG/US-100-DNS

### Diagrams and graphs

excess gain graph



Article no longer available - archive entry