




Fibre-optic amplifier

OUF-HPKG/6M

Article no longer available - archive entry



Product characteristics

Type of light		infrared light
Housing		rectangular
Dimensions	[mm]	28 x 16 x 56

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	< 35; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[m]	< 0.12; (Through-beam sensor)
Range	[mm]	< 40; (Diffuse reflection sensor)
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

OU5039




Fibre-optic amplifier

OUF-HPKG/6M

Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	653
Mechanical data		
Housing		rectangular
Dimensions	[mm]	28 x 16 x 56
Materials		PPO modified
Lens alignment		side lens
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		Angle bracket: 1, E20211 screwdrivers
Remarks		
Remarks		light-on mode corresponds to the NC output function for through-beam fibre optics corresponds to the NO output function for diffuse-reflection fibre optics
Pack quantity		1 pcs.
Electrical connection		
Cable: 6 m, PVC; 3 x 0.34 mm ²		

Connection



Core colours :

BN = brown
BU = blue
BK = black



Fibre-optic amplifier

OUF-HPKG/6M

Diagrams and graphs

excess gain graph

