




Fibre optic through beam sensor

FE-00-P-V-M4

Article no longer available - archive entry

Alternative article: E20059 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



Application	
Function principle	Through-beam sensor
Detection zone	
Range with fibre optic amplifier type	OKF; OUF
OKF	
Range of fibre optics [mm]	120
OUF	
Range of fibre optics [mm]	120
Operating conditions	
Ambient temperature [°C]	-20...80

E20117



Fibre optic through beam sensor

FE-00-P-V-M4

Mechanical data	
Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	600
Min. bending radius [mm]	20
Materials	Adapter: PPE
Fibre material	glass
Fibre head material	stainless steel (1.4305 / 303)
Fibre sheath material	PVC
Remarks	
Pack quantity	1 pcs.

Article no longer available - archive entry

Alternative article: E20059 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!