

RC6022




Incremental encoder with solid shaft

RC-0040-I24/L2

Article no longer available - archive entry

Discontinuation date: 31.03.2016



- 1 reference mark
- 2 M3 Depth 5 mm



Product characteristics

Resolution	40 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Application

Function principle	incremental
--------------------	-------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 150

Outputs

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	300
Type of short-circuit protection	< 60 s
Phase difference A and B [°]	90

Measuring/setting range

Resolution	40 resolution
------------	---------------

Operating conditions

Ambient temperature [°C]	-40...100
Note on ambient temperature	for firmly laid cable: -40 °C
Max. relative air humidity [%]	98
Protection	IP 64; (on the housing: IP 67; on the shaft: IP 64)



Incremental encoder with solid shaft

RC-0040-I24/L2

Tests / approvals		
Shock resistance		200 g
Vibration resistance		30 g
MTTF	[years]	190
Mechanical data		
Weight	[g]	479.6
Dimensions	[mm]	Ø 58 / L = 44.6
Materials		aluminium
Max. revolution, mechanical	[U/min]	16000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Remarks		
Notes		discontinued article
Electrical connection		
Cable: 2 m, PUR; Maximum cable length: 300 m; radial, can also be used axially		
brown	A	
green	A inverted	
grey	B	
pink	B inverted	
red	0 index	
black	0 index inverted	
blue	L+ sensor	
white	0V sensor	
brown/green	L+ (Up)	
white/green	0V (Un)	
lilac	failure inverted	
screen	housing	
Diagrams and graphs		
Pulse diagram		<p>Output A</p> <p>Output B</p> <p>0 index</p>

RC6022

Incremental encoder with solid shaft

RC-0040-I24/L2



Article no longer available - archive entry

Discontinuation date: 31.03.2016