

RM7003



Absolute multiturn encoder with solid shaft

RMS0025-C24/E

Article no longer available - archive entry

Alternative articles: RM7011

When selecting an alternative article and accessories please note that technical data may differ!



1 M4 Depth 5 mm



Product characteristics

Resolution	8192 steps; 4096 revolutions; 25 bit
Communication interface	CAN
Shaft design	solid shaft
Shaft diameter [mm]	6

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	9...36 DC
Current consumption [mA]	< 250
Reverse polarity protection	yes

Outputs

Short-circuit protection	yes
Code	binary

Measuring/setting range

Resolution	8192 steps; 4096 revolutions; 25 bit
------------	--------------------------------------



Absolute multiturn encoder with solid shaft

RMS0025-C24/E

Accuracy / deviations		
Accuracy	± 1 LSB	
Software / programming		
Parameter setting options	CAN parameter; scaling; preset; Baud rate; direction of rotation; address	
Addressing	address selector switch; Software	
Interfaces		
Communication interface	CAN	
CAN		
Protocol	CANopen; DSP - 406	
Operating conditions		
Ambient temperature	[°C]	-40...70
Protection	IP 66; (on the housing: IP 67; on the shaft: IP 67)	
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Weight	[g]	663.6
Dimensions	[mm]	Ø 58 / L = 90.5
Materials	aluminium	
Max. revolution, mechanical [U/min]	6000	
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design	solid shaft	
Shaft diameter	[mm]	6
Shaft material	steel (1.4104)	
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange	synchro-flange	
Electrical connection		
terminal strip in the terminal chamber: ; Maximum cable length: 25 m; 100 m (500 kb/s)		