


Evaluation unit with display for PT100/PT1000 temperature sensors

TR-...KDBR12-QFRKG/US/...../V

phase-out article

Alternative articles: TR7439

When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 programming button
- 4 connector for temperature sensor M12 x 1



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-40...300 °C	-40...572 °F
Communication interface	IO-Link	
Process connection	threaded connection G 1/2 external thread	

Application

Special feature	Gold-plated contacts
Application	for Pt100 and Pt1000 measuring elements

Electrical data

Operating voltage	[V]	18...32 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------



Evaluation unit with display for PT100/PT1000 temperature sensors

TR-...KDBR12-QFRKG/US/...../V

Outputs		
Total number of outputs	2	
Output signal	switching signal; IO-Link; (configurable)	
Electrical design	PNP/NPN	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]	2	
Permanent current rating of switching output DC [mA]	250	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Measuring range	-40...300 °C	-40...572 °F
Set point SP	-39.8...300 °C	-39.6...572 °F
Reset point rP	-40...299.8 °C	-40...571.6 °F
In steps of	0.1 °C	0.1 °F
Resolution		
Resolution of switching output [K]	0.1	
Resolution of display [K]	0.1	
Accuracy / deviations		
Switch point accuracy [K]	± 0,3	
Display accuracy [K]	± 0,3	
Temperature drift per 10 K [K]	0.1	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.0	
Operating conditions		
Ambient temperature [°C]	-25...70	
Storage temperature [°C]	-40...85	
Protection	IP 67	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-5 Surge	1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]	240	
Mechanical data		
Weight [g]	232.6	



Evaluation unit with display for PT100/PT1000
temperature sensors

TR-...KDBR12-QFRKG/US/...../V	
Materials	stainless steel (304/1.4301); stainless steel (303/1.4305); EPDM/X; PC; PBT; FKM
Process connection	threaded connection G 1/2 external thread

Displays / operating elements		
Display	Display unit	2 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



- 1: two-wire sensor
- 2: three-wire sensor
- 3: four-wire sensor
- B: link