


## Flow sensor for connection to an evaluation unit

STR12ABA/US-100-H

Article no longer available - archive entry



## Product characteristics

Process connection	G 1/2 external thread
--------------------	-----------------------

## Application

Application	high-temperature range
Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

## Liquids

Application	high-temperature range
Medium temperature [°C]	-25...80

## Gases

Medium temperature [°C]	-25...80
-------------------------	----------

## Electrical data

Connection to control monitor	VS 0100
-------------------------------	---------

## Measuring/setting range

## Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

## Gases

Setting range [cm/s]	5...15
----------------------	--------

## Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

## Response times

Response time [s]	1...10
-------------------	--------

# ST3004



## Flow sensor for connection to an evaluation unit

STR12ABA/US-100-H


Liquids		
Response time	[s]	1...10
Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		threaded type
Materials		stainless steel (1.4305 / 303)
Process connection		G 1/2 external thread
Remarks		
Pack quantity		1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



### Connection



BN =            Core colours :  
WH =            brown  
YE =            white  
GN =            yellow  
                  green