


E80408



RFID tag

ID-TAG/8.3X3.6/06



monteringshål: Ø 8,0 x 3,7 mm



Applikation		
Driftstemperatur (aktiv)	[°C]	-40...85
Topptemperatur (passiv)	[°C]	90
Elektriska data		
Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	896
Minnestyp		EEPROM
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		100000
Driftförhållanden		
Omgivningstemperatur	[°C]	-40...85
Lagringstemperatur	[°C]	-40...90
Kapslingsklass		IP 68
Godkännanden / tester		
Radiogodkännande		ISO 15693
Mekaniska data		
Vikt	[g]	3,75
Monteringstyp		Presspassningshus; Installation i metall; Installation i icke-metal
Mått	[mm]	Ø 8,3 / L = 3,6
Material		kapsling: PPS GF30; epoxy
Anmärkning		
Förpackning		10 antal