


E80380



RFID tag

ID-TAG/30X2,8/03 - 64 Kbit



Applikation

Driftstemperatur (aktiv)	[°C]	-25...85
Topptemperatur (passiv)	[°C]	90

Elektriska data

Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	65536
Minnestyp		FRAM
Chiptyp		MB89R112
Antal block		256
Blockstorlek	[Byte]	32
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		obegränsat

Driftförhållanden

Omgivningstemperatur	[°C]	-25...85
Lagringstemperatur	[°C]	-40...90
Kapslingsklass		IP 68; IP 69K

Godkännanden / tester

Radiogodkännande	ISO 15693
------------------	-----------

Mekaniska data

Vikt	[g]	3,85
Monteringstyp		installation på icka metalliska material; (skruv ; limmas på en yta)
Mått	[mm]	Ø 30 / L = 3
Material		PPA [ISO 1874: PA6T/6I-GF50]

Anmärkning

Förpackning	1 antal
-------------	---------



RFID tag

ID-TAG/30X2,8/03 - 64 Kbit

Ytterligare data

avläsningssavstånd vid montage icke-metall (mm)

ANT410 / DTI410	15
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	30
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	25
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	40
ANT513 / DTI513 / DTC510	65
ANT515 / DTI515 / ANT516 / DTI516	30
ANT600 / DTI600	115