




RFID tag

ID-TAG/D50x3, 0/0 2528 bit



Applikation

Driftstemperatur (aktiv)	[°C]	-40...85
Topptemperatur (passiv)	[°C]	90

Elektriska data

Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	1024
Minnestyp		EEPROM
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		100000

Driftförhållanden

Omgivningstemperatur	[°C]	-40...85
Lagringstemperatur	[°C]	-40...90
Kapslingsklass		IP 68; IP 69K

Godkännanden / tester

Stöttålighet	DIN IEC 68-2-27	40 g 18 ms
Vibrationstålighet	DIN IEC 68-2-6	10 g 10...2000 Hz
Radiogodkännande		ISO 15693

Mekaniska data

Vikt	[g]	11,55
Monteringstyp		installation på ick metalliska material; (skruv ; limmas på en yta)
Mått	[mm]	Ø 50 / L = 3
Material		PPA svart

Anmärkning

Förpackning	1 antal
-------------	---------



RFID tag

ID-TAG/D50x3,0/0 2528 bit

Ytterligare data

avläsningsavstånd vid montage icke-metall (mm)

ANT410 / DTI410	15
ANT411 / DTI411	25
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	15
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	50
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	35
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	65
ANT513 / DTI513 / DTC510	90
ANT515 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	190