



A2LA / ILAC MRA - kalibreringscertifikat för
temperaturgivare n-punkters

A2LA-KALIBRIERUNG TEMP. N-PKT

Werkskalibrierschein
Factory calibration certificate

Messumformer-Typ: PT1000
transmitter type: PT1000
Serien-Nr.: 10000000
serial no.: 10000000
Messbereich: 0...100 °C
temperature range: 0...100 °C
Ausgangssignal: 4...20 mA
output: 4...20 mA
Genauigkeit: ±0,1 °C
accuracy: ±0,1 °C
Kalibrierdatum: 10.05.2015
date of calibration: 10.05.2015

Auftragsnummer: 100000
job no.: 100000
Referenzgerät: PT1000
reference unit: PT1000
Prüfnorm, Temperatur: PTB 700
testing device, temperature: PTB 700
Serien-Nr.: 10000000
serial no.: 10000000
PTB-Zertifikat: PTB 700
PTB certificate: PTB 700
Umgebungstemperatur: 20 °C
ambient temperature: 20 °C

The calibration was performed in accordance with the requirements of the PTB 700 standard. The calibration was performed in accordance with the requirements of the PTB 700 standard. The calibration was performed in accordance with the requirements of the PTB 700 standard.

The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C.

The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C.

The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C.

The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C. The accuracy of the measurement is ±0,1 °C.

Mekaniska data	
Vikt	[g] 19,171
Anmärkning	
Anmärkning	Kalibreringscertifikatet måste beställas i samband med en givare. Motsvarande givare levereras tillsammans med kalibreringscertifikatet. Kalibreringscertifikatet är utfärdat på två språk (tyska/engelska). Efterföljande order är endast möjlig om givaren är i ett rent skick vid återlämnandet. I internetversionen av databladet finns exempel på ett certifikat under fliken "Nedladdningar". max. 4 mätpunkter kan väljas enligt kundens önskemål