
E80348

RFID tag

ID-TAG/TRIANGLE HOUSING/06



1 ID tag
2 tag position mark middle of the antenna

Application		
Application		coding of workpiece carriers in routing conveyors
Operating temperature (active)	[°C]	-25...85
Peak temperature (passive)	[°C]	90
Electrical data		
Operating frequency	[MHz]	13,56
Memory size	[bit]	896
Memory type		EEPROM
Chip type		Vigo
Number of blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693
Max. read cycles		unlimited
Max. write cycles		100000
Operating conditions		
Ambient temperature	[°C]	-25...85
Storage temperature	[°C]	-40...90
Protection		IP 67

E80348

RFID tag

ID-TAG/TRIANGLE HOUSING/06

Tests / approvals			
Shock resistance		DIN IEC 68-2-29	30 g 18 ms
Vibration resistance		DIN IEC 68-2-6	6 g 14...200 Hz
Radio approval		ISO 15693	
Mechanical data			
Weight	[g]	9.1	
Housing		tag fixture for workpiece carriers	
Type of mounting		Installation on metal and non-metal materials; (screw fastening ; sticking to a surface)	
Dimensions	[mm]	18 x 33 x 16.9	
Materials		PBT orange; PA black	
Accessories			
Items supplied			
Remarks			
Pack quantity		1 pcs.	

Other data

read distance when mounted on metal (mm)

ANT410 / DTI410	4
ANT411 / DTI411	5
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	-
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	10
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	5
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	15
ANT513 / DTI513 / DTC510	20
ANT515 / DTI515 / ANT516 / DTI516	5
ANT600 / DTI600	15