


Muting arm set

2X-THROUGH-BEAM-SENSORS



- 1 plug blue
 2 plug red
 T transmitter
 R receiver



Product characteristics

Type of light	infrared light
---------------	----------------

Application

Design	crossbeam muting with two through-beam sensors
Function principle	Through-beam sensor

Electrical data

Operating voltage [V]	19.2...28.8 DC
Current consumption [mA]	120; (transmitter: 60; receiver: 60)
Protection class	III
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	940

Outputs

Electrical design	PNP
Output function	dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	0.5
Permanent current rating of switching output DC [mA]	100
Short-circuit protection	yes
Overload protection	yes




Muting arm set


2X-THROUGH-BEAM-SENSORS

Detection zone		
Range	[m]	< 2.5
Operating conditions		
Ambient temperature	[°C]	-30...55
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	3000
Materials		aluminium; polypropylene
Lens material		polycarbonate-ABS
Remarks		
Pack quantity		4 pcs.
Electrical connection - receiver 1		

Connector: 1 x M12; coding: A; Moulded body: blue



Connection



4 OUT switching output




Muting arm set


2X-THROUGH-BEAM-SENSORS

Electrical connection - receiver 2

Connector: 1 x M12; coding: A; Moulded body: red




Connection



4 OUT switching output

Electrical connection - transmitter 1


Connector: 1 x M12; coding: A; Moulded body: blue



Muting arm set

2X-THROUGH-BEAM-SENSORS


Connection




2 IN Sync A

Electrical connection - transmitter 2

Connector: 1 x M12; coding: A; Moulded body: red



Connection



2 IN Sync B