

SBY34BF0BPKG/US



Number of inputs and outputs	Number of digital outputs: 1
Process connection	Rp 3/4

Media		Liquids; water; glycol solutions; coolants
Medium temperature	[°C]	0...85
Pressure rating	[bar]	40
Pressure rating	[MPa]	4

Operating voltage	[V]	10...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Total number of outputs	1
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1
Output function	normally open



Flow sensor with integrated backflow prevention

SBY34BF0BPKG/US

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Short-circuit protection		yes
Overload protection		yes
Measuring/setting range		
Setting range	[l/min]	1...15
Accuracy / deviations		
Repeatability		1
	[% of the final value]	
Hysteresis	[l/min]	0,2...1
Measuring error		± 5
	[% of the final value]	
Response times		
Response time	[s]	< 0.01
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	3318
Mechanical data		
Weight	[g]	559.6
Materials		brass chemically nickel-plated; PP; aluminium anodised; PA
Materials (wetted parts)		stainless steel (301/1.4310); stainless steel (304/1.4301); PBT; brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM
Process connection		Rp 3/4
Switching cycles mechanical		10 million
Displays / operating elements		
Display	switching status	4 x LED, yellow
Accessories		
Items supplied		Allen key
Remarks		
Remarks		Caution Do not turn the cap beyond the maximum value of the setting range.
		All data refer to water (20 °C).
Pack quantity		1 pcs.

Flow sensor with integrated backflow prevention

SBY34BF0BPKG/US

Electrical connection

Connector: 1 x M12; coding: A




Connection



Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity