
SF1200

Flow sensor for connection to an evaluation unit

SFM12ABB

Article no longer available - archive entry

Alternative articles: SF5350 + E40101
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Process connection		M12 x 1
Application		
Application		high-temperature range
Media		Liquids; Gases
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Liquids		
Application		high-temperature range
Medium temperature	[°C]	-25...80
Gases		
Medium temperature	[°C]	-25...80
Electrical data		
Connection to control monitor		VS 0200
Measuring/setting range		
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Gases		
Setting range	[cm/s]	200...2000
Greatest sensitivity	[cm/s]	200...800
Accuracy / deviations		
Temperature gradient	[K/min]	15
Response times		
Response time	[s]	1...10
Liquids		
Response time	[s]	1...10

SF1200


Flow sensor for connection to an evaluation unit

SFM12ABB

Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		threaded type
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Materials		stainless steel (1.4571/316Ti)
Materials (wetted parts)		stainless steel (1.4571/316Ti)
Process connection		M12 x 1
Accessories		
Items supplied		sealings: 2 x AMF 30
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Cable: 2 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm², PVC

Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey