


Buton capacitiv iluminat

KTMDF-KGRBPKG/US



Caracteristicile produsului

Model electric	PNP
Functii de iesire	normal deschis
Dimensiuni [mm]	Ø 29 / L = 31

Aplicatie

Principiu de operare	dinamic
----------------------	---------

Date electrice

Tensiune de lucru [V]	12...30 DC
Consum de energie [mA]	30
Clasa de protectie	III
Protectie la polaritate inversa	da
Timpul maxim de intarziere la pornire [ms]	500

Iesiri

Model electric	PNP
Functii de iesire	normal deschis
Curentul permanent pe iesirea de comutare DC [mA]	200
Protectie la scurtcircuit	da
Protectie suprasarcina	da
Lungimea semnalului de iesire [ms]	300

Timpi de raspuns

Timp reactie [ms]	35
-------------------	----

Condițiile mediului

Temperatură de ambianță [°C]	-40...85
Protectie	IP 65; IP 67; IP 69K; (frontal)

KT5112



Buton capacitiv iluminat

KTMDF-KGRBPKG/US

Teste / certificari		
Ecranare electromagnetica	IEC 61000-4	
Date mecanice		
Greutate	[g]	55
Dimensiuni	[mm]	Ø 29 / L = 31
Materiale	PA 6.6-GF30 negru; Suprafata de actionare: PA Grilamid TR 90UV	
Afisaj / elemente de operare		
Display	Stare de functionare	1 x LED, rosu
	functie	1 x LED, verde poate fi declansat
Accesorii		
Articole livrate	piulite de blocare: 1	
	Garnitura: 1	
Accesorii (optional)	Disc cu simbol	
Observatii		
Unitate de ambalare	1 buc.	
Conectare electrica - mufa		
Cablul: 0,3 m, PUR		
Conector: 1 x M12; codificare: A		



Racord

