




RFID tag

ID-TAG/7.5X1.0/06



Applikation

Driftstemperatur (aktiv)	[°C]	-40...85
Topptemperatur (passiv)	[°C]	85

Elektriska data

Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	896
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693

Driftförhållanden

Omgivningstemperatur	[°C]	-40...85
Lagringstemperatur	[°C]	-40...85
Kapslingsklass		IP 68

Godkännanden / tester

Stöttålighet	DIN IEC 68-2-27	40 g (18 ms)
Vibrationstålighet	DIN IEC 68-2-6	10 g (10...2000 Hz)

Mekaniska data

Vikt	[g]	2,1
Mått	[mm]	Ø 7,5 / L = 1
Material		kapsling: Epoxydharz

Anmärkning

Förpackning		10 antal
-------------	--	----------



RFID tag

ID-TAG/7.5X1.0/06

Ytterligare data

avläsningssavstånd vid montage icke-metall (mm)

ANT410 / DTI410	10
ANT411 / DTI411	10
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	20
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	15
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	25
ANT513 / DTI513 / DTC510	30
ANT515 / DTI515 / ANT516 / DTI516	10
ANT600 / DTI600	-