


E80407



RFID tag

ID-TAG/86X54/06



Applikation

Driftstemperatur (aktiv)	[°C]	-30...50
--------------------------	------	----------

Elektriska data

Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	896
Minnestyp		EEPROM
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		100000

Driftförhållanden

Omgivningstemperatur	[°C]	-30...50
Kapslingsklass		IP 67

Godkännanden / tester

Stöttålighet	DIN IEC 68-2-27	40 g 18 ms
Vibrationstålighet	DIN IEC 68-2-6	10 g 10...2000 Hz
Radiogodkännande		ISO 15693

Mekaniska data

Vikt	[g]	57,2
Mått	[mm]	54 x 86 x 1
Material		PVC

Anmärkning

Förpackning		10 antal
-------------	--	----------



RFID tag

ID-TAG/86X54/06

Ytterligare data

avläsningsavstånd vid montage icke-metall (mm)

ANT410 / DTI410	22
ANT411 / DTI411	35
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	20
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	65
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	50
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	85
ANT513 / DTI513 / DTC510	120
ANT515 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	230