




RFID tag

ID-TAG/20X3/06-16KBit



Applikation

Applikation	Kodning av lastbärare i industriella transportsystem	
Driftstemperatur (aktiv) [°C]		-25...85
Topptemperatur (passiv) [°C]		85

Elektriska data

Arbetsfrekvens [MHz]		13,56
Minnesstorlek [bit]		16000
Minnestyp		FRAM
Chiptyp		MB89R118C
Antal block		250
Blockstorlek [Byte]		8
Unikt identifikationsnummer (UID) [Byte]		8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		obegränsat

Driftförhållanden

Omgivningstemperatur [°C]		-25...85
Lagringstemperatur [°C]		-40...85
Kapslingsklass		IP 68

Godkännanden / tester

Stöttålighet	DIN IEC 68-2-27	40 g 18 ms
Vibrationstålighet	DIN IEC 68-2-6	10 g 10...2000 Hz

Mekaniska data

Vikt [g]		9,3
Mått [mm]		Ø 20 / L = 3
Material		PPA

Anmärkning

Förpackning		5 antal
-------------	--	---------



RFID tag

ID-TAG/20X3/06-16KBit

Ytterligare data

avläsningssavstånd vid montage icke-metall (mm)

ANT410 / DTI410	10
ANT411 / DTI411	15
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	30
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	25
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	35
ANT513 / DTI513 / DTC510	50
ANT515 / DTI515 / ANT516 / DTI516	25
ANT600 / DTI600	-