




RFID tag

ID-TAG/R20X2,5/06



Applikation

Driftstemperatur (aktiv)	[°C]	-40...85
Topptemperatur (passiv)	[°C]	90; (längd av test: 1 x 100 h)

Elektriska data

Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	2528
Minnestyp		EEPROM
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		100000

Driftförhållanden

Omgivningstemperatur	[°C]	-40...85
Lagringstemperatur	[°C]	-40...90
Kapslingsklass		IP 68

Godkännanden / tester

Radiogodkännande		ISO 15693
------------------	--	-----------

Mekaniska data

Vikt	[g]	2,9
Monteringstyp		installation på icke metalliska material; (limmas på en yta)
Mått	[mm]	Ø 20 / L = 3
Material		PPA

Anmärkning

Förpackning		1 antal
-------------	--	---------



RFID tag

ID-TAG/R20X2,5/06

Ytterligare data

avläsningssavstånd vid montage icke-metall (mm)

ANT410 / DTI410	14
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	12
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	30
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	25
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	40
ANT513 / DTI513 / DTC510	50
ANT515 / DTI515 / ANT516 / DTI516	25
ANT600 / DTI600	110