




RFID tag

ID-TAG/Tear Shape/06



Applikation		
Applikation	Kodning av lastbärare i industriella transportsystem	
Driftstemperatur (aktiv)	[°C]	-25...55
Topptemperatur (passiv)	[°C]	75
Elektriska data		
Arbetsfrekvens	[MHz]	13,56
Minnesstorlek	[bit]	896
Minnestyp		EEPROM
Chiptyp		ICODE SLIX
Antal block		28
Blockstorlek	[Byte]	4
Unikt identifikationsnummer (UID)	[Byte]	8
RFID-standard		ISO 15693
Max. läscykler		obegränsat
Max. skrivcykler		100000
Driftförhållanden		
Omgivningstemperatur	[°C]	-25...55
Lagringstemperatur	[°C]	-25...75
Kapslingsklass		IP 66
Godkännanden / tester		
Stöttålighet	DIN IEC 68-2-27	40 g 18 ms
Vibrationstålighet	DIN IEC 68-2-6	10 g 10...2000 Hz
Radiogodkännande		ISO 15693
Mekaniska data		
Vikt	[g]	21,6
Monteringstyp		installation på icke metalliska material; (klämfäste)
Mått	[mm]	40 x 31 x 4,8
Material		ABS
Anmärkning		
Förpackning		5 antal



RFID tag

ID-TAG/Tear Shape/06

Ytterligare data

avläsningssavstånd vid montage icke-metall (mm)

ANT410 / DTI410	10
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	15
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	40
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	30
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	45
ANT513 / DTI513 / DTC510	60
ANT515 / DTI515 / ANT516 / DTI516	30
ANT600 / DTI600	80