


Cylinder sensor for tie-rod cylinder

IQ5006/US-100

Article no longer available - archive entry



1 Sensing face

Product characteristics

Electrical design	PNP
Output function	normally open

Application

Special feature	Magnetic-field immune
Magnetic-field immune	yes

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 2
Reverse polarity protection		yes
Max. power-on delay time	[ms]	35

Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	20
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



Cylinder sensor for tie-rod cylinder

IQ5006/US-100

Detection zone		
Response sensitivity	[mT]	2...35
Travel speed	[m/s]	< 10
Accuracy / deviations		
Hysteresis	[mm]	1
Repeatability	[mm]	0.1
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)
Mechanical data		
Cylinder type		pneumatic cylinders
Materials		plastics
Displays / operating elements		
Display	switching status	1 x LED, red
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		

Connector: 1 x M12; coding: A



Connection

