



Inductive sensor

IZB30,8-BPKG/V2A/0,3M/AS-610




illustration (example)



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	0.8
Housing	cylindrical
Dimensions [mm]	Ø 4 / L = 30

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	0.8
Real sensing range Sr [mm]	0.8 ± 10 %
Operating distance [mm]	0...0.65

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 65

IZ5044



Inductive sensor

IZB30,8-BPKG/V2A/0,3M/AS-610

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	2053


Mechanical data		
Weight	[g]	18.5
Housing		cylindrical
Mounting		flush mountable
Dimensions	[mm]	Ø 4 / L = 30
Materials		stainless steel (303/1.4305); sensing face: POM

Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories		
Items supplied		Mounting clamps: 1

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug		
Cable: 0.3 m, PUR		
Connector: 1 x M8; coding: A; Locking: snap-fit		



Connection

