

DTE914



Compact RFID device

DTRUHFA HLRWETUS04



- 1 LED operating status
- 2 LED bar display fieldbus interface
- 3 Mounting thread M4 max. insertion depth 15mm

Application

Radio approval for China

Electrical data

Operating voltage	[V]	19.2...28.8 DC
Current consumption	[mA]	500
Power consumption	[W]	8.6
Protection class		III
Operating frequency	[MHz]	920,5...924,5
RFID standard		EPC Class1 GEN2/ISO 18000-63
Transmission power EIRP	[mW]	200; (maximum: 250 mW)

Outputs

Max. current load per output [mA] 100; (max.)

Interfaces

Communication interface Ethernet

Ethernet - TCP/IP

Protocol	TCP/IP
Factory settings	IP address: 192.168.0.79 subnet mask: 255.255.255.0 gateway IP address: 192.168.0.100
Usage type	parameter setting; data transmission

Operating conditions

Ambient temperature	[°C]	-20...55
Note on ambient temperature		with mounting plate and cooling element: -20...60 °C
Storage temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump 50 g (11 ms) / single shock
------------------	----------------	---

DTE914



Compact RFID device

DTRUHFA HLRWETUS04

Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
----------------------	--------------	-------------------

Mechanical data

Weight	[g]	691.15
Dimensions	[mm]	113 x 118.6 x 50
Materials	housing: aluminium; PBT / PC; stainless steel	

Displays / operating elements

Display	power supply	1 x LED, green
	LED bar display	4 x LED, yellow signal strength ID tag
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - Ethernet

Connector: 2 x M12; coding: D




ETH1 / ETH2

1	TD+
2	RD+
3	TD-
4	RD-

Electrical connection - power supply

Connector: 1 x M12; coding: A



PWR

1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used