


M9H202



Cylinder sensor

M9B3002BBPKG/B/AM/500/1M/AMP



Application

Application	hydraulic cylinders
Media	detects ferrous metals
Min. bursting pressure [bar]	2000
Pressure rating [bar]	500

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 23
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.6
Max. leakage current [mA]	0.1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	2
--------------------	---

Accuracy / deviations

Hysteresis [% of Sr]	< 15
Switch point drift [% of Sr]	10
Repeatability [% of Sr]	10

M9H202



Cylinder sensor

M9B3002BBPKG/B/AM/500/1M/AMP

Operating conditions		
Pressure peak	[bar]	1000
Ambient temperature	[°C]	-25...85
Protection		IP 65; IP 68; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
	DIN ISO 11452-5	100 V/m
Vibration resistance	EN 60068-2-6 Fc	20 g 50 sweep cycles per frequency; 1 octave per minute in 3 axes / 10...3000 Hz -20...50 °C
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes / -40...85 °C
	EN 60068-2-27 Ea	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes / -20...50 °C
MTTF	[years]	925
Mechanical data		
Weight	[g]	82.5
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M14 x 1.5 / L = 41
Thread designation		M14 x 1.5
Materials		housing: stainless steel stainless steel (1.4404 / 316L); O-ring: FKM
Tightening torque	[Nm]	< 25
Full-metal housing		yes
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

M9H202



Cylinder sensor

M9B3002BBPKG/B/AM/500/1M/AMP

Electrical connection

Cable: 1 m, PUR; 3 x 0.34 mm²

Connection



Core colours :

BK = black

BN = brown

BU = blue

Connector: 1 x AMP ((282105-1))