




## Through-beam sensor receiver

OGE-DPKG/6M



### Product characteristics

Type of light	red light
Housing	threaded type

### Application

Function principle	Through-beam sensor
--------------------	---------------------

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10
Protection class	II
Reverse polarity protection	yes
Type of light	red light

### Outputs

Electrical design	PNP
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	150; (200 (...60 °C))
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

### Detection zone

Transmitter / receiver	receiver
Range [m]	< 20
Range adjustable	no

### Operating conditions


Ambient temperature [°C]	-25...80
Protection	IP 65; IP 67; IP 68; IP 69K



## Through-beam sensor receiver

OGE-DPKG/6M

Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	1112
Mechanical data		
Weight	[g]	255.8
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 68.6
Thread designation		M18 x 1
Materials		housing: stainless steel (316L/1.4404); Sealing: EPDM
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Remarks		operating voltage "supply class 2" according to cULus
Pack quantity		1 pcs.
Electrical connection		
Cable: 6 m, PVC; 3 x 0.34 mm <sup>2</sup>		
Connection		



Core colours :

BK = black

BN = brown

BU = blue



## Through-beam sensor receiver

OGE-DPKG/6M

### Diagrams and graphs

excess gain graph

