




Retro-reflective sensor

OUP-HNKG/US-100-DNO

Article no longer available - archive entry



receiver in upper lens
transmitter in lower lens

Product characteristics

Type of light	red light
Housing	rectangular
Dimensions [mm]	28 x 16 x 51

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage [V]	10...50 DC
Current consumption [mA]	30; ((24 V))
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	660

Outputs

Electrical design	NPN
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	160
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [m]	< 1.5; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Polarisation filter available	yes

OU5098



Retro-reflective sensor

OUP-HNKG/US-100-DNO


Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		Angle bracket
Remarks		
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12



Connection



Article no longer available - archive entry