


PT504E



Pressure transmitter

PT-010-SEG14-A-ZVG/US



Product characteristics				
Number of inputs and outputs	Number of analogue outputs: 1			
Measuring range	0...10 bar	0...145 psi	0...1000 kPa	0...1 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			
Application				
Application	for mobile applications			
Media	liquids and gases			
Medium temperature	-40...125			
Min. bursting pressure	300 bar	4350 psi	30 MPa	
Pressure rating	25 bar	360 psi	2.5 MPa	
Note on pressure rating	static			
Vacuum resistance	-1000			
Type of pressure	relative pressure			
Electrical data				
Operating voltage	[V]	8...32 DC		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 0.1		
Inputs / outputs				
Number of inputs and outputs	Number of analogue outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analogue signal			
Number of analogue outputs	1			
Analogue current output	[mA]	4...20		
Max. load	[Ω]	(U _b - 8 V) / 21,5 mA; @8V = 0 Ω; @12V max. 200 Ω; @24V max. 750 Ω		

PT504E



Pressure transmitter

PT-010-SEG14-A-ZVG/US

Short-circuit proof		yes			
Overload protection		yes			
Measuring/setting range					
Measuring range		0...10 bar	0...145 psi	0...1000 kPa	0...1 MPa
Accuracy / deviations					
Repeatability [% of the span]		< ± 0,05; (with temperature fluctuations < 10 K)			
Characteristics deviation [% of the span]		< ± 0,8; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)			
Linearity deviation [% of the span]		< ± 0,25 (BFSL) / < ± 0,5 (LS)			
Hysteresis deviation [% of the span]		< ± 0,2			
Long-term stability [% of the span]		< ± 0,1; (per 6 months)			
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)			
Temperature coefficient span [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)			
Response times					
Step response time analogue output [ms]		2			
Operating conditions					
Ambient temperature [°C]		-40...100			
Storage temperature [°C]		-40...100			
Protection		IP 67; IP 69K			
Tests / approvals					
EMC		compliant with UN ECE R10, rev. 5		(E1 compliant)	
		ISO 11452-2		100 V/m	
		DIN EN 61326-1			
Shock resistance		DIN EN 60068-2-27		500 g (1 ms)	
Vibration resistance		DIN EN 60068-2-6		20 g (10...2000 Hz)	
MTTF [years]		711			
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data					
Weight [g]		58.5			
Materials		stainless steel (630/1.4542/17-4 PH); stainless steel (316L/1.4404); PEI			
Materials (wetted parts)		stainless steel (630/1.4542/17-4 PH)			
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)			
Tightening torque [Nm]		25...35; (recommended tightening torque; depends on lubrication, seal and pressure rating)			
Process connection		threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			
Process connection sealing		HNBR (DIN EN ISO 1179-2)			
Restrictor element integrated		yes			

PT504E



Pressure transmitter

PT-010-SEG14-A-ZVG/US

Remarks


Remarks	BFSL = Best Fit Straight Line LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A




Connection



OUT analogue output
 colours to DIN EN 60947-5-2
 Core colours :
BN = brown
WH = white

Diagrams and graphs

characteristic load curve of current output



1: Max. load
2: min. load