

RU-0100-I24/A2

Article no longer available - archive entry



Resolution	100 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	150

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	300
Type of short-circuit protection	< 60 s
Phase difference A and B [°]	90

Resolution	100 resolution
------------	----------------

Ambient temperature	[°C]	-30...85
Note on ambient temperature		for firmly laid cable: -30 °C
Storage temperature	[°C]	-30...100
Protection		IP 64



Incremental encoder with solid shaft

RU-0100-I24/A2

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data


Dimensions [mm]	Ø 58 / L = 46
Materials	aluminium
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20
Fixing flange	synchro-flange

Electrical connection

Cable: 2 m, PUR; axial

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
lilac	failure inverted
screen	housing

Diagrams and graphs

Pulse diagram	 Output A Output B 0 index
---------------	---