




Inductive sensor

IFB3002-BPKG/V2A/10-55V/3M/BH



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	2
Housing		threaded type
Dimensions	[mm]	M12 x 1
Application		
Special feature		Halogen-free
Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	125; (150 (...50 °C))
Short-time current rating of switching output	[mA]	150
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes

IF5955



Inductive sensor

IFB3002-BPKG/V2A/10-55V/3M/BH

Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	2418
Mechanical data		
Weight	[g]	113.8
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Materials		housing: stainless steel (303/1.4305); sensing face: PBT; end cap: TPE
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.

IF5955




Inductive sensor

IFB3002-BPKG/V2A/10-55V/3M/BH

Electrical connection

Cable: 3 m, PUR, Halogen-free; 3 x 0.34 mm²

Connection



	Core colours
BN	brown
BK	black
BU	blue