II5913

Inductive analogue sensor

IIK3015A1PKG/US




phase-out article

Alternative articles: II6913

When selecting an alternative article and accessories please note that technical data may differ!

With IO-Link



C€ CK

Product characteristics					
Housing		threaded type			
Dimensions	[mm]	M30 x 1.5 / L = 70			
Electrical data					
Operating voltage	[V]	1530 DC			
Current consumption	[mA]	< 20			
Protection class		II			
Reverse polarity protection		yes			
Outputs					
Analogue current output	[mA]	420; (linear; gradient: 1,143 mA/mm; for frontal approach and for target made of mild steel: 45 x 45 x 1 mm)			
Max. load	[Ω]	500			
Short-circuit protection		yes			
Overload protection		yes			
Detection zone					
Measuring range	[mm]	115			
Accuracy / deviations					
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3			
Linearity error of analogue output	[%]	± 1 %; (of IA max)			
Repeatability analogue output	[%]	± 1 %; (of IA max)			
Response times					
Response time	[ms]	< 20			

II5913

Inductive analogue sensor





Operating conditions				
Ambient temperature	[°C]	-2580		
Protection		IP 67		
Tests / approvals				
EMC		EN 60947-5-2		
MTTF	[years]		964	
Mechanical data				
Weight	[g]	125.42		
Housing		threaded type		
Mounting		non-flush mountable		
Dimensions	[mm]	M30 x 1.5 / L = 70		
Thread designation		M30 x 1.5		
Materials		housing: brass white bronze coated; sensing face: PBT		
Tightening torque	[Nm]	50		
Displays / operating el	ements			
Display		within the operating range	1 x LED, yellow lights	
		outside the operating range	1 x LED, yellow flashing	
Accessories				
Items supplied		lock nuts: 2		
Remarks				
Pack quantity		1 pcs.		
Electrical connection -	plug			

Connector: 1 x M12; coding: A



Connection

