


AC1253



AS-Interface power supply

PSU-3AC/ASi-8A



1 LED AS-i ok



Electrical data

Frequency AC	[Hz]	47...64
Operating voltage tolerance	[%]	15...20
Nominal voltage AC	[V]	400
Input voltage range AC	[V]	380...480
Protection class		I
Overvoltage protection		yes; (< 36 V)
Max. power-on delay time	[ms]	90
Output voltage AS-i	[V]	30.5
Output power (permanent)	[W]	244
Output power (peak)	[W]	256
Note on output power (peak)	[W]	briefly to load bus capacities after power on
Power factor (nominal voltage 400 V AC / 50 Hz)		0.53
Power factor (nominal voltage 480 V AC / 50 Hz)		0.52
Power reserve	[%]	5
Number of output circuits		1
Output current AS-i	[A]	8
Max. residual ripple	[mV]	90



AS-Interface power supply

PSU-3AC/ASI-8A

Switch-on peak current (nominal voltage 400 V AC / 60 Hz)	[A]	4
Switch-on peak current (nominal voltage 480 V AC / 50 Hz)	[A]	4
Efficiency (nominal voltage 400 V AC / 60 Hz)	[%]	92
Efficiency (nominal voltage 480 V AC / 50 Hz)	[%]	92.1
External input protection		$\leq B-6 A / \leq C-3 A$
Derating	[W/K]	6 (60...70 °C)
Mains buffering time (nominal voltage 400 V AC / 60 Hz)	[ms]	34
Mains buffering time (nominal voltage 480 V AC / 50 Hz)	[ms]	53
Input current (nominal voltage 400 V AC / 60 Hz)	[A]	0.7
Input current (nominal voltage 480 V AC / 50 Hz)	[A]	0.6
Power loss (nominal voltage 400 V AC / 60 Hz)	[W]	21.2
Power loss (nominal voltage 480 V AC / 50 Hz)	[W]	20.9
Integrated data decoupling		yes
Back feeding protection	[V]	35

Outputs

Short-circuit proof	yes
Overload protection	yes
Overload performance	output current constant
Parallel connection of outputs possible	no
Series connection of outputs possible	no

Operating conditions

Ambient temperature	[°C]	-25...70
Note on ambient temperature	observe the free space for convection (see operating instructions)	
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	95; (IEC 60068-2-30)
Protection		IP 20
Pollution degree		2; (IEC 62103: conductive soiling not permitted)

Tests / approvals

EMC	EN 61000-6-1	
	EN 61000-6-2	
	EN 61000-6-3	
	EN 61000-6-4	
Vibration resistance	IEC 60068-2-6	$\pm 1,6 \text{ mm } 2...17,8 \text{ Hz} / 2 \text{ g } 17,8...500 \text{ Hz}$
Shock resistance	IEC 60068-2-27	30 g 6 ms / 20 g 11 ms
Power Factor Correction (PFC)		met



AS-Interface power supply

PSU-3AC/ASi-8A

AS-i classification

AS-i certificate	98401
------------------	-------

Mechanical data

Weight	[g]	950
Type of mounting		rail; (TH35 (EN 60715))
Dimensions	[mm]	124 x 62 x 120
Materials		steel sheet

Displays / operating elements

Display	AS-i voltage	LED, green
---------	--------------	------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

screw terminals:


Connection



- 1: primary
2: secondary

Diagrams and graphs


block diagram






output characteristics

Output Voltage



characteristic curve for degree of efficiency / power loss


Efficiency





characteristic line for derating

Allowed Output Current



characteristic line for mains buffering time

Hold-up Time

