




AS-Interface CANopen gateway with PLC

ControllerE 2Mstr CO RS232

Article no longer available - archive entry

Alternative articles: AC1332
When selecting an alternative article and accessories please note that technical data may differ!



Application	
Application	decentralised controller; CANopen gateway
Electrical data	
Operating voltage [V]	24 DC
Current consumption [mA]	< 500
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Interfaces	
Communication interface	RS232; CAN
CAN	
Protocol	CANopen



AS-Interface CANopen gateway with PLC

ControllerE 2Mstr CO RS232

RS232		
Transmission rate	9600...115200 Baud	
Connector type	RJ11	
Note on interfaces	electrically isolated	
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection	IP 20	
AS-i classification		
AS-i version	2.1	
AS-i profile	M3	
Mechanical data		
Housing	housing for DIN rail mounting	
Materials	aluminium; steel sheet galvanised	
Displays / operating elements		
Display	function	4 x LED, red
		3 x LED, green
		3 x LED, yellow
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connection		

