




C-slot cylinder sensor

MKC3028BBPKG/G/0,57M/ZH

Article no longer available - archive entry



- 1 fastening clamp
- 2 Sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	17.5 x 2.8 x 7.7

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	30

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Response sensitivity [mT]	2.8
Travel speed [m/s]	> 10

Accuracy / deviations

Hysteresis [mm]	< 1.5
Repeatability [mm]	< 0.2

MK5316



C-slot cylinder sensor

MKC3028BBPKG/G/0,57M/ZH

Operating conditions

Ambient temperature	[°C]	-25...85
Protection		IP 65; IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B

Mechanical data

Mounting	non-flush mountable
Type of mounting	fastening clamps with hexagon socket, width across flats 0.9
Cylinder type	C-slot cylinders
Dimensions	[mm] 17.5 x 2.8 x 7.7
Materials	PA; fastening clamp: stainless steel

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Accessories (optional)	Allen key
------------------------	-----------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 0.57 m, PUR; 3 x 0.08 mm²

Connection



BK = Core colours :
BN = black
BU = brown
 blue