



Diffuse reflection sensor

OPT-FPKG/TS-700

Article no longer available - archive entry

No scale drawing available

Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Special feature	Function check output
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	20; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Function check output		yes
Max. current load for function check output	[mA]	50
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	80
Short-circuit protection		yes
Type of short-circuit protection		pulsed

OP5044



Diffuse reflection sensor

OPT-FPKG/TS-700

Overload protection	yes
---------------------	-----

Detection zone

Range [mm]	< 3000; (white paper 200 x 200 mm)
------------	------------------------------------

Range adjustable	yes
------------------	-----

Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

Protection	IP 65
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular
---------	-------------

Dimensions [mm]	86 x 28 x 142
-----------------	---------------

Materials	PPO modified
-----------	--------------

Lens material	glass
---------------	-------

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x Ø 28 mm; coding: A



Connection



2 Function check output